

OVERVIEW STANDARD SIZES/SPECS PER IMAGESETTER

Film-Recorder	Light	RapidAccess	HardDot	Width										Length	Spec			Sheet size
																	Roomlight Load	
Agfa-Compugraphic																		
Phoenix 2000	LDR 635	HNS//HNm	HND/ I-FRM / I-FR7M	25,4	35,6	40,6	46,0	47,3	48,3	50,8				x76,25m	610CD			
Phoenix 2250	LDR 635	HNS//HNm	HND/ I-FRM / I-FR7M	25,4	35,6	40,6	46,0	47,2	48,3	50,8	57,2			x76,25m	610CD			
Phoenix News	LDR 635	HNS//HNm	HND/ I-FRM / I-FR7M	25,4	35,6	40,6	46,0	47,2	48,3					x76,25m	610CD			
CG 9500 / 9600	HeNe 633	HNS		20,3	25,4	30,5	33,8							x30,5m			600D	
CG 9700		HNS		20,3	25,4	30,5	33,8	46,5						x30,5m				
SelectSet 5000	HeNe 633	HNS//HNm	HND/ I-FRM / I-FR7M		25,4	33,8	40,6							x76,25m	600BD			
SelectSet 7000	HeNe 633	HNS//HNm	HND/ I-FRM / I-FR7M	33,8	40,6	66,0								x76,25m	600BD			
AccuSet 800 / 1000 / 1200 / 1400 / 1500 (W)	LDR 670	HNS/HNm	HND/ I-FRM	25,4	30,5	33,8	35,6							x76,25m	600BD			
AVANTRA 20	LDR 650	HNS//HNm	HND/ I-FRM / I-FR7M		25,4	30,5	33,8	35,6						x76,25m	600BD			
AVANTRA 25 / 25E / 25S / 25XT	LDR 650	HNS//HNm	HND/ I-FRM / I-FR7M		25,4	30,5	33,8	35,6	40,6	45,7	46,0			x76,25m	600BD			
AVANTRA 30 /30E /30S	LDR 650	HNS//HNm	HND/ I-FRM / I-FR7M	35,6	40,6	45,7	50,8	61,0	66,0	71,1	72,4	76,2		x76,25m	600BD			
AVANTRA 36 / 36S / 44 / 44S / 44XT	LDR 650	HNS//HNm	HND/ I-FRM / I-FR7M	40,6	45,7	50,8	55,9	61,0	66,0	72,4	76,2	91,4		x76,25m	600BD			
Avanxis IV	LDR 635	HNS//HNm	HND/ I-FRM / I-FR7M	30,5	35,5	40,6	45,7	50,8	55,9	61,0				x60m		600CDH		
Avanxis VIII	LED 660	LDD	LDD	61,0	66,0	71,0	80,0	83,8						x60m		610CDH		
CG 9400 / 9400PS / StudioSet 2000 / 2000SR	iLD 780	IR		20,3	25,4	30,5	33,8							x30,5m			600D	
Elan 500	iLD 780	IR		20,3	30,5	31,0								x25m	600BD			
ProSet 9550 / 9800	iLD 780	IR		20,3	25,4	30,5	33,8							x76,25m	600BD			
Antares 1000 / Antares 1000XT	YAG 532	AR (depleted)															68,5 x 93,9	
Antares 1600	YAG 532	AR (depleted)															91,4x111,7	
Autologic Information International																		
APS-Colormaster / MAGNUM/RS	Ar 488	AR (depleted)		43,0	53,0	55,0	71,9	76,2	81,2	82,0				x60m		600CDH		
	HeNe 633	HNS/HNm	HND/ I-FRM	43,0	53,0	54,9	71,9	76,2	81,2	82,0				x60m		600CDH		
	iLD 780	IR		43,0	53,0	55,0	71,9	76,2	81,3	82,0				x60m		600CDH		
APS-Colormaster / Mercur	Ar 488	AR (depleted)		40,6	46,0	55,0	62,0							x60m		600CDH		

	HeNe 633	HNS/HNm	HND/ I-FRM	40,6	46,0	54,9	62,0							x60m		600CDH		
	iLD 780	IR		40,6	46,0	55,0	62,0							x60m		600CDH		
APS-Colormaster / HS / RS	Ar 488	AR (depleted)		25,0	34,0	53,0	54,9	55,0						x60m		600CDH		
APS-Colormaster / HS / NP / RS	iLD 780	IR		25,0	34,0	53,0	55,0							x60m		600CDH		
APS-6/80 / APS-6/80C / APS-6/84C	HeNe 633	HNS/ HNm	HND/ I-FRM	25,0	31,0	35,5								x60m		600BD		
APS-6/108 / C / CH / CHS / FS / FC	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	35,5	43,0	46,0							x60m		600BD		
APS-6/70C / CH / CHS	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	31,0									x30m		600BD		
APS-5000	HeNe 633	HNS/ HNm	HND/ I-FRM / I-FR7M		25,4	33,8	40,6							x60m/ x120,00m		600BD		
APS-7000	HeNe 633	HNS/ HNm	HND/ I-FRM / I-FR7M	33,8	40,6	66,0								x120,00m		600BD		
Laser PAGESetter 3800 HR / 3810 HR	HeNe 633	HNS/ HNm	HND/ I-FRM	31,0	38,1	40,0	44,0							x120,00m		610BD		
APS-6/82 ACS / APS-6/84 ACS	LDR 670	HNS/ HNm	HND/ I-FRM	25,4	30,5	33,8	35,5							x60m/ x120,00m		600BD		
APS-6/3850/ 6/3850T / Grafix 3825	LDR 670	HNS/ HNm	HND/ I-FRM	25,0	35,5	35,6	38,1	40,0	44,0					x120,00m		610BD		
APS-3850 SST Wide Imager	LDR 670	HNS/ HNm	HND/ I-FRM	35,5	35,6	38,1	40,0	44,0	49,8	63,5	68,6			x120,00m		610BD		
APS-7/20 AV	LDR 650	HNS/ HNm	HND/ I-FRM		25,4	30,5	33,8	35,5						x60m		600BD		
APS-7/25 AV / AV25E	LDR 650	HNS/ HNm	HND/ I-FRM / I-FR7M		25,4	30,5	33,8	35,5	40,6	45,7	46,0			x60m		600BD		
APS-7/30 AV	LDR 650	HNS/ HNm	HND/ I-FRM / I-FR7M	35,5	40,6	45,7	50,8	56,0	61,0	66,0	72,4	76,2				600BD		
APS-7/36 AV / AV36S	LDR 650	HNS/ HNm	HND/ I-FRM / I-FR7M	40,6	45,7	50,8	56,0	61,0	66,0	72,4	76,2	91,4				600BD		
APS-7/44 AV / AV44S	LDR 650	HNS/ HNm	HND/ I-FRM / I-FR7M	40,6	45,7	50,8	56,0	61,0	66,0	72,4	76,2	91,4				600BD		
APS-6/70 VR	iLD 780	IR		30,5	31,0									x30,5m				600D
APS-6/84 VR	iLD 780	IR		30,5	31,0	35,5								x60m		600BD		
APS-6/108 VR	iLD 780	IR		31	35,6	46,0								x60m		600BD		
BARCO Graphics / (Esko-Graphics)																		
BG 3400	HeNe 633	HNS/ HNm	HND/ I-FRM / I-FR7M															35.5x45.7
BG 3500 / BG 3600 / BG 3700 / BG 3704	HeNe 633	HNS/ HNm	HND/ I-FRM / I-FR7M															27.9x35.5
		HNS/ HNm	HND/ I-FRM / I-FR7M															35.6x52.1
		HNS/ HNm	HND/ I-FRM / I-FR7M															54.1x64.8
BG 3800 / BG 7404 / BG 7412 / BG 7424	HeNe 633	HNS/ HNm	HND/ I-FRM / I-FR7M															52.1x64.8
		HNS/ HNm	HND/ I-FRM / I-FR7M															80.0x110
BG 3800 C	HeNe 633	HNS/ HNm	HND/ I-FRM / I-FR7M															61.0x81.3
BG 3900 MegaSetter	HeNe 633		I-FR7M															120.0x161.2
BG 3700 M / BG 7304 M	HeNe 633	HNS/ HNm	HND/ I-FRM / I-FR7M															57.2x64.8
GigaSetter	HeNe 633		I-FR7M	161,2										x30,5m		610C		
MegaSetter Plus	HeNe 633		I-FR7M															81.3x111.7
			I-FR7M															96.5x116.8
			I-FR7M															101.6x127.0
			I-FR7M															106.7x132.0

			I-FR7M																111.7x132.0
			I-FR7M																101.6x142.2
			I-FR7M																116.8x142.2
			I-FR7M																120.0x161.2
			I-FR7M																132.0x147.3
			I-FR7M																127.0x161.2
			I-FR7M																135.0x161.2
			I-FR7M																135.0x161.2
LithoSetter III	YAG 532	AR (depleted)																	42.5x55.0
																			81.0x110.0
LithoSetter V	YAG 532	AR (depleted)																	47.5x60.0
Viking 6	VLD 405	AR (depleted)																	76.2x76.2
Viking 8	VLD 405	AR (depleted)																	81.2x111.7
MidiSetter 30	LDR 650	HNS/ HNm	HND/ I-FRM / I-FR7M	35,6	40,6	45,7	50,8	55,9	61	66	72,4	76,2	x76,25m	600BD					
MidiSetter 44S	LDR 650	HNS/ HNm	HND/ I-FRM / I-FR7M	40,6	45,7	50,8	55,9	61	66	72,4	76,2	91,4	x76,25m	600BD					
Berthold																			
4P Recorder	Ar 488	AR (depleted)		25,0	34,0	43,0	53,0	55,0					x60m					600CDH	
4P Recorder	iLD 780	IR		25,0	34,0	43,0	53,0	55,0					x60m					600CDH	
Laser Recorder Li / Li-100 / Li-80S	HeNe 633	HNS		30,5	31,0								x30,5m	600BD					
SelectSet 5000	HeNe 633	HNS/ HNm	HND/ I-FRM		25,4	33,8	40,6						x60m/ x76,25m	600BD					
SelectSet 7000	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8	40,6	66,0							x76,25m	600BD					
AccuSet 1000	LDR 670	HNS/ HNm	HND/ I-FRM	25,4	30,5	33,8	35,5						x60m/ x76,25m	600BD					
Plus Monotype System Film-Recorder																			
Bidco																			
FP 80 C / FP 80 CH / FP 480 MCS	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	35,5								x60m	600BD					
FP100C /100 U /109 CS /CD / FP 108 MCS	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	35,5	46,0							x60m	600BD					
Mach 2	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	35,5	46,0							x60m	600BD					
Birmy Graphics																			
Birmy Setter 300 TXF	HeNe 633	HNS/ HNm		30,5	31,0								x30m	600BD					
BirmySetter 450 HN	HeNe 633	HNS	HND/ I-FRM	30,5	35,5	43,0	46,0						x60m	600BD					
BirmySetter 350 Z	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	35,5								x60m	600BD					
BirmySetter 300 / 300 X	iLD 780	IR		30,5	31,0								x30,5m	600BD					
BirmySetter 400 / 400 Turbo	iLD 780	IR		31,0	40,0								x30m/60m	600BD					
BirmyPowerSet 3600	iLD 780	IR		31,0	35,6								x60m	600BD					

BirmyPowerSet 4600/4400	iLD 780	IR		31,0	35,6	46,0								x60m	600BD			
BirmySetter 340 Turbo	iLD 780	IR		30,5	33,8									x30,5m	600BD			
BirmySetter PowerSet A3	iLD 780	IR		33,8										x30,5m	600BD			
Chelgraph																		
IBX W 1000 L / LS	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	35,5	43,0	46,0							x60m	600BD			
IBX 3000 / IBX 1500 L	HeNe 633	HNS		30,5	31,0									x30,5m	600BD			
IBX 2540 L	iLD 780	IR		30,5	31,0									x30,5m			600D	
Chemco																		
Chemco S-300	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5										x60m	610CD			
NewScan 1500 Recorders	Ar 488	AR (depleted)		56,0	61,0									x60m	610CD			
Créo Products																		
Créo Platesetter 3244 / 3244 F	YAG 532	AR (depleted)																81.2x111.7
Creo (CréoScitex)																		
Dolev 100 / 200 / 250	HeNe 633	HNS/ HNm	HND/ I-FRM	38,1										x60m	610CD			
Dolev 400 PSI / 440 / 440F / 450 / 450F	HeNe 633	HNS/ HNm	HND/ I-FRM	66,0										x60m	610CD			
Dolev 800 - HeNe 633	LDR 650	HNS/ HNm	HND/ I-FRM	30,5	50,8	76,2	83,8							x60m	600CD			
Dolev 800 V / 800V2 / 800E / 800V3 / 800V4	LDR 650	HNS/ HNm	HND/ I-FRM	30,5	50,8	76,2	83,8	86,3						x60m	600CD			
Dolev 800 LF	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	35,5	40,6	45,7	50,8	55,9	66,0				x60m	600CD			
Dolev 800V2 UHR / 800V4 UHR	LDR 650	HNS/ HNm	HND/ I-FRM	30,5	50,8	76,2	83,8	86,3						x60m	600CD			
Dolev 4press / 4pressV / 4pressV2	LDR 650	HNS/ HNm	HND/ I-FRM	35,6	38,1	50,8	55,9	66,0	73,7	74,9				x60m	610CD			
Dolev 4pressVXL	LDR 650	HNS/ HNm	HND/ I-FRM	35,6	38,1	50,8	55,9	66,0	73,7	74,9	76,2	81,2		x60m	610CD			
Dolev 4news / 4newsV	LDR 650	HNS/ HNm	HND/ I-FRM	35,6	38,1	50,8	55,9	66,0	73,7	74,9				x60m	610CD			
Dolev 4newsVXL	LDR 650	HNS/ HNm	HND/ I-FRM	35,6	38,1	50,8	55,9	66,0	73,7	74,9	76,2	81,2		x60m	610CD			
Dolev 2pressPlus	LDR 650	HNS/ HNm	HND/ I-FRM	25,4	30,5	38,1	40,6	55,9						x60m	610CD			
Rimon 44/55	LDR 635	HNS/ HNm	HND/ I-FRM	66,0	76,2	81,3	83,8	127,0						x60m	600CD			
Rimon 50/66	LDR 635	HNS/ HNm	HND/ I-FRM	66,0	76,2	81,3	83,8	127,0						x60m	600CD			
Dolev 2DRY	iLD 780			30,5	35,5	40,6								x60m	610CD			
Dolev 4DRY / 4DRYPlus	iLD 780			35,5	38,0	50,8	55,8	66,0	73,7	74,9				x60m	610CD			
Cron																		
ACF- 3604 HC	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	31,0	45,7								x60m	610BD			
ACF- 3602 H	HeNe 633	HNS/ HNm	HND/ I-FRM	45,7	50,8	61,0	63,5	66,0						x60m	610BD			
Crosfield																		

MagnaScan																			
630-640 / 625-645 / 626-656 / Sirius 250	Ar488	AR (depleted)		65,7	71,0									x60m	610CD				65.9x71.0
640M / 635-645M / 636-676M / Sirius 250M	Ar488	AR (depleted)		84,7	105,7									x60m	610CD				84.7x105.9
MagnaSetter 850M	Ar488	AR (depleted)		84,7	105,7									x60m	610CD				84.7x105.9
Autoloader 656E / MagnaSetter 750	Ar488	AR (depleted)		71,0										x60m	610CD				
StudioWriter 1000 / MagnaSetter 2000	Ar488	AR (depleted)		35,5	50,8	66,0	71,9	111,7						x60m	600CD				
Pagefax K664 / StudioWriter 650	Ar488	AR (depleted)		45,7										x60m	610CD				
MagnaSetter 620	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8	52,0									x60m	600BD				
MagnaSetter 350 / 355	iLD 780	IR		15,2	20,3	25,4	33,0							x60m	600CD				
Cymbolic Sciences-Gretag Imaging																			
PlateJet Emerald 4up-B2	YAG 532	AR (depleted)																	68.5x101.1
PlateJet Emerald / PlateJet Sapphire	YAG 532	AR (depleted)																	91.4x111.7
Du Pont																			
ImPower XEL 500	LDR 635	HNS/ HNm	HND/ I-FRM	35,5	40,6	45,7	50,8	55,9						x60m		600CDH			
ImPower XEL 1000	iLD 780	IR		61,0	66,0	71,0	76,2	81,3						x60m		610CDH			
HDR 450	LDR 670	HNS/ HNm	HND/ I-FRM	35,0	37,0	46,0								x60m		610CDH			
Highlight 12	HeNe 633	HNS/ HNm	HND/ I-FRM	25,0	31,0									x60m	600BD				
Highlight 18	HeNe 633	HNS/ HNm	HND/ I-FRM	25,0	31,0	46,0	51,0							x60m	600BD				
XEL 140 / XEL 140 HS	LDR 670	HNS/ HNm	HND/ I-FRM	31,0	35,5									x60m	600BD				
XEL 180 / XEL 180 HS	LDR 670	HNS/ HNm	HND/ I-FRM	31,0	35,5	46,0								x60m	600BD				
XEL 400	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	33,8	35,5	40,6	45,7	46,0				x60m/ x76,25m	600BD				
ECRM Imaging Systems																			
Autokon 1030/News720/1000/2000/8400/PB72	HeNe 633	HNS		20,3	25,4	30,5								x30,5m				600D	
Autokon / PelBox 2030 / 2530 / 3030	HeNe 633	HNS		30,5	31,0									x30m	600BD				
PelBox 3000 / ScriptSetter	HeNe 633	HNS		30,5	31,0									x30m	600BD				
PelBox 1045 / 1245 / 1545 CS	HeNe 633	HNS/ HNm	HND / IFRm	30,5	35,5	43,0	46,0							x60m	600BD				
PelBox1045 HS / 108 / 108 S	HeNe 633	HNS/ HNm	HND / IFRm	30,5	35,5	43,0	46,0							x60m	600BD				
Mako 108 HT	HeNe 633	HNS/ HNm	HND / IFRm	30,5	31,0	33,8	35,5	36,8	40,6	45,7	46,0			x60m/ x76,25m	600BD				
Marlin 2500 / Marlin 46	HeNe 633	HNS/ HNm	HND / IFRm	30,5	31,0	33,8	35,5	36,8	40,6	45,7	46,0			x60m/ x76,25m	600BD				
Marlin 3500 / Stingray 46	LDR 670	HNS/ HNm	HND / IFRm	30,5	31,0	33,8	35,5	36,8	40,6	45,7	46,0			x60m/ x76,25m	600BD				
Mako 3600 / 3625 / 3650 / 3675 / Mako 36	LDR 670	HNS/ HNm	HND / IFRm	30,5	31,0	33,8	35,5							x60m/ x76,25m	600BD				
Mako 4600 / 4625 / 4650 / 4675 / Mako 46	LDR 670	HNS/ HNm	HND / IFRm	30,5	31,0	33,8	35,5	36,8	40,6	45,7	46,0			x60m/ x76,25m	600BD				
ID 36 DrumSetter	LDR 670	HNS/ HNm	HND / IFRm	30,5	31,0	35,5								x60m	600BD				
PelBox 3850 / 3850 DM / 3850 HS	LDR 670	HNS/ HNm	HND / IFRm	31,0	35,6	35,5	40,0	44,0						x60m/ x76,25m	610BD				
ScriptSetter VRL-30 / Sunfish	LDR 670	HNS		30,5	31,0									x30m	600BD				

ScriptSetter VRL-36 / VRL-36 HS / Sunfish 36	LDR 670	HNS/ HNm	HND / IFRm	30,5	31,0	35,5								x60m	600BD			
Sunfish 40	LDR 670	HNS/ HNm	HND / IFRm	31,0	35,5	40,6								x60m	600BD			
ScriptSetter VRL-45 / VRL-45 HS	LDR 670	HNS/ HNm	HND / IFRm	30,5	31,0	35,5	46,0							x60m	600BD			
KnockOut 4550 L/PRF / Stingray 46	LDR 670	HNS/ HNm	HND / IFRm	30,5	31,0	33,8	35,5	36,8	40,6	45,7	46,0			x60m/ x76,25m	600BD			
StingRay 5200 / Stingray 52	LDR 670	HNS/ HNm	HND / IFRm	35,5	40,6	45,7	46,0	47,0	50,8	51,0	52,0			x60m/ x76,25m	600BD			
StingRay 6300 / Stingray 63 / 63QS	LDR 670	HNS/ HNm	HND / IFRm	35,5	40,6	45,7	50,8	53,0	55,9	61,0	62,5	63,5		x60m/ x76,25m	600BD			
StingRay 6300 HS / Marlin 63	HeNe 633	HNS/ HNm	HND / IFRm	35,5	40,6	45,7	50,8	53,0	55,9	61,0	62,5	63,5		x60m/ x76,25m	600BD			
Bluefin 63	HeNe 633	HNS/ HNm	HND / IFRm	46,0	48,0	49,0	52,0	55,0	55,8	60,0	61,0	63,5		x60m/ x76,25m		610CDH		
Mako 5625 / Mako 56	LDR 670	HNS/ HNm	HND / IFRm	35,5	40,6	45,0	45,7	46,0	50,8	51,0	52,0	55,9		x60m/ x76,25m	600BD			
ScriptSetter VR-30	iLD 780	IR		30,5	31,0									x25m	600BD			
ScriptSetter VR-36 / VR-36 HS	iLD 780	IR		30,5	31,0	35,5								x60m	600BD			
ScriptSetter VR-45 HS	iLD 780	IR		30,5	31,0	35,5	46,0							x60m	600BD			
KnockOut 4550	iLD 780	IR		30,5	31,0	33,8	35,5	40,6	46,0					x60m	600BD			
Mako Oasis 3650 / Mako 36 Dry	iLD 780	IR		30,5	33,8	35,5								x60m	600BD			
Mako Oasis 4650 / Mako 46 Dry	iLD 780	IR		30,5	33,8	35,5	40,6	46,0						x60m	600BD			
Eikonix																		
LaserRecorder 8601	He-Cd 442	AR (depleted)		50,8										x60m	610CD			50.8x61.0
Escher-Grad																		
EG-5000 ImageSetter	LDR 635	HNS/ HNm	HND/ I-FRM	35,5	40,6	50,8	66,0							x60m	600CD			
EG-2000 Laser-Plotter	LDR 635	HNm	I-FRM / I-FR7M															
EG-2200 / 1000 / 5000 Laser-Plotter	LDR 635	HNm	I-FRM / I-FR7M															
EG-2205	LDR 635	HNm	I-FRM / I-FR7M															
		HNm	I-FRM / I-FR7M															
		HNm	I-FRM / I-FR7M															
EG-8000 ImageSetter	LDR 635	HNS/ HNm	HND/ I-FRM / I-FR7M	40,6	46,0	50,8	66,0	76,2						x60m	600CD			
EG-8200 ImageSetter	LDR 635	HNS/ HNm	HND/ I-FRM / I-FR7M	46,0	50,8	76,2	81,3							x60m	600CD			
EG-9000 / 9400 ImageSetter	LDR 635	HNm	I-FRM / I-FR7M	66	76,2	81,3	83,8	127						x60m	600CD			111.7x127.0
Eskofot																		
EskoSet 2230	LDR 670	HNS/ HNm	HND/ I-FRM	40,0	43,0	46,0	49,0	52,0	55,0					x60m		610CD		
EskoSet 3600 / 1622	LDR 670	HNS/ HNm	HND/ I-FRM	25,0	25,4	30,5	33,8	35,5	40,6	42,0				x60m/ x76,25m	600BD			
Esko-Graphics																		
BG 3800 MegaSetter	HeNe 633	HNm	I-FRM / I-FR7M															52.0x64.8

		HNm	I-FRM / I-FR7M														80.0x110
		HNm	I-FRM / I-FR7M														133.3x161.2
																	135.0x161.2
GigaSetter	HeNe633		I-FR7M	161,2										x30,5m	610C		
MAGNUM B1 Ctf / MAGNUM B1 Ctf-HS	Ar 488	AR (depleted)		35,6	53,0	55,0	71,9	76,2	81,2	82,0				x60m		600CDH	
MAGNUM B1 Ctf / MAGNUM B1 Ctf-HS	HeNe633	HNS/ HNm	HND/ I-FRM	35,6	45,7	53,0	54,9	55,9	71,9	76,2	81,3	82,0		x60m		600CDH	
DotMate 6500P	LDR 670	HNS/ HNm	HND/ I-FRM	33,9	37,0	40,0	43,0	46,0	48,0					x60m		610CDH	
DotMate 4900	LDR 670	HNS/ HNm	HND/ I-FRM	35,6										x60m		610BD	
DPX-5080	LDR 670	HNS/ HNm	HND/ I-FRM	35,5										x76,25m		610BD	
DPX-5080	LDR 670	HNS/ HNm	HND/ I-FRM	35,6										x60m		610CD	
DPX-Genesis	iLD 760	IR		31,0										x30,5m			600D
Extra Imaging Systems																	
MaxxSetter 400 / ExpressSetter 400	LDR 670	HNS/ HNm	HND/ I-FRM	40,0	40,0									x60m/ x76,25m		600BD	
ExxtraSetter 300 / ExpressSetter 300	LDR 670	HNS/ HNm	HND/ I-FRM	33,8										x60m		600BD	
MaxxSetter 300	LDR 670	HNS/ HNm	HND/ I-FRM	33,8										x60m		600BD	
ExxtraSetter Exxcalibur / ExxcaliburXX	LDR 635	HNS/ HNm	HND/ I-FRM	35,6	38,1	40,0	43,0	45,7	49,8	50,8	63,5	66,0		x76,25m		610BD	
ExxtraSetter 300 / Exxpress 300	iLD 780	IR		33,8										x30m		600BD	
ExxtraSetter Maxxima 300	iLD 780	IR		33,8										x60m		600BD	
ExxtraDRY 300 / DrySetter 300	iLD 780	IR		33,8										x60m		600BD	
FUJIFILM Electronic Imaging FFEI																	
Celix 8000 / 8200	Ar 488	AR (depleted)		35,6	50,8	66,0	71,9	111,7						x60m		600CD	600CDH
Celix 2000	LDR 670	HNS/ HNm	HND/ I-FRM	35,6										x60m		600CD	600CDH
Celix 4000	LDR 670	HNS/ HNm	HND/ I-FRM	35,6	50,8	66,0	76,2							x60m		600CD	600CDH
FD-3100	iLD 780	IR		50,8	61,0	66,0	71,1	76,2	81,3					x60m/ x76,25m			610CDH
LuxSetter 5600V	HeNe 633		HND/ I-FRM	33,0	50,8	55,9								x60m			600CDH
Sumo Luxel F-9000	LDR 635	HNS/ HNm	HND/ I-FRM	55,9	76,8	91,4	106,7	113,0						x60m			610CDH
Luxel F-4080	LDR 635	HNS/ HNm	HND/ I-FRM	55,9	67,0	76,8								x60m			610CDH
Luxel F-6000 (Ninja)	LDR 635	HNS/ HNm	HND/ I-FRM	35,6	52,0	55,9	67,0	71,9	76,8					x60m			610CDH
Pi 1400 / Pi 1400 H	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	35,5								x60m		600BD	
Pi 1800 / Pi 1800 H	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	35,5	46,0							x60m		600BD	
Pi 2800 / Pi-M 2800H	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	33,8	35,5	40,6	45,7	46,0				x60m/ x76,25m		600BD	
Pi-M 1400 /1400H/ 1400S / 1400SS	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	35,5								x60m/ x76,25m		600BD	
PiM 1800 / 1800H / 1800S /1800SS	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	33,8	36,8	40,6	45,7	46,0				x60m/ x76,25m		600BD	
FUJI Photo Film																	

Scanart 30 II	Ar 488	AR (depleted)		30,5								x60m	610CD			
JUJIX Scanart Recorder RC 330* / SC 230	iLD 780	IR		15,2	20,3	25,4	33,0*					x60m	600CD			
FUJIX Scanart Recorder RC 450 II	iLD 780	IR		25,4	33,0	40,6	45,7					x60m	600CD			
Gerber System Corporation																
Crescent / 42 PlateSetter	Ar 488	AR (depleted)														50.8x66.0
		AR (depleted)														81.2x106.6
GraphoTech																
GraphoTech SpeedSetter	LDR 670	HNS/ HNm	HND/ I-FRM	40,0	40,0							x60m/ x76,25m	600BD			
Harris Graphics																
Digiform 3500 / Digiform 3600	HeNe 633	HNm	I-FRM / I-FR7M													27.9x35.5
		HNm	I-FRM / I-FR7M													35.6x52.1
		HNm	I-FRM / I-FR7M													52.0x64.8
Digiform 3800	HeNe 633	HNm	I-FRM / I-FR7M													52.0x64.8
		HNm	I-FRM / I-FR7M													80.0x110
Heidelberg PrePress (Linotype-Hell)																
ChromaGraph DC 300 ER / DC 350 ER	Ar 488	AR (depleted)														40.6x50.8
		AR (depleted)														40.6x51.5
ChromaGraph CP 340 / CR 402 / 345 ER	Ar 488	AR (depleted)		111,7								x60m	610CD			
ChromaGraph CTX 330 / 501	Ar 488	AR (depleted)		111,7								x60m	610CD			
ChromaGraph CP 341 ER / 345	Ar 488	AR (depleted)		76,2								x60m	610CD			
ChromaGraph C 399 ER / DC 360	Ar 488	AR (depleted)														
ChromaGraph DC 370 / DC 380	Ar 488	AR (depleted)														51.5x66.5
ChromaGraph CR 401 ER	Ar 488	AR (depleted)														55.9x75.0
ChromaGraph R 3020 / LTC 830	Ar 488	AR (depleted)		54,9								x60m		610CDH		
ChromaGraph R 3030 / LTC 930 / 3060 PS	Ar 488	AR (depleted)		54,9	111,7							x60m		610CDH		
Pressfax Recorder P 200 / P 210 / LS 210	Ar 488	AR (depleted)		31,0	34,0	43,0	46,0	50,8				x60m	600CD			
Linotronic Recorder 630	LDR 670	HNS/ HNm	HND/ I-FRM	33,9	37,0	46,0						x60m		610CDH		
Herkules PRO / Herkules ELITE / BASIC	LDR 670	HNS/ HNm	HND/ I-FRM	46,0	55,0	67,0	76,2					x60m		610CDH		
Herkules M / Herkules M PRO	LDR 670	HNS/ HNm	HND/ I-FRM	33,9	37,0	46,0	55,0					x60m		610CDH		
Herkules NP PRO	LDR 670	HNS/ HNm	HND/ I-FRM	33,9	37,0	46,0	55,0	58,0	62,0			x60m		610CDH		
SignaSetter / SignaSetter Pro	HeNe 633	HNS/ HNm	HND/ I-FRM	46,0	55,0	61,0	67,0	76,2	81,2	107,9		x60m		610CDH		
Primesetter 74	LDR 660	HNS/ HNm	HND/ I-FRM	36,0	46,0	49,0	52,0	55,0	67,0	76,2		x60m		610CDH		
Primesetter 102	LDR 660	HNS/ HNm	HND/ I-FRM	46,0	49,0	52,0	54,9	60,0	67,0	76,2	85,0	107,9	x60m		610CDH	
Linotronic 300 / 330	HeNe 633	HNS/ HNm	HND/ I-FRM	24,0	31,0							x60m	600BD			

Linotronic 500 / 530 / 560	HeNe 633	HNS/ HNm	HND/ I-FRM	25,0	31,0	43,0	46,0	51,0					x60m	600BD			
Linotronic 100 / 100P / 101 Ommitech 2100	HeNe 633	HNS		20,3	25,4	30,5							x30m				600D
QUASAR / Duosetter	LDR 670	HNS/ HNm	HND/ I-FRM	28,0	31,0	34,0	47,0	53,0	54,0				x60m	600BD			
Linotronic MARK 30 EX	LDR 670	HNS		31,0	35,5	40,0							x30,5m	600BD			
Quicksetter / Quicksetter 400	LDR 670	HNS/ HNm	HND/ I-FRM	25,0	31,0	33,8	35,5	40,6					x60m/ x76,25m	600BD			
Quicksetter 460	LDR 670	HNS/ HNm	HND/ I-FRM	25,0	31,0	33,8	35,5	40,6	45,7	46,0			x60m/ x76,25m	600BD			
Quicksetter 350 / Quicksetter 46	LDR 670	HNS/ HNm	HND/ I-FRM	25,0	31,0	33,8	35,5						x60m/ x76,25m	600BD			
Linotronic 200P / SQ 200 / 230 / LTC 260	iLD 780	IR		30,5	31,0								x30,5m				600D
Bridgit 70 / LTC 170 / Linotronic MARK 10	iLD 780	IR		31,0									x30,5m	600BD			600D
Bridgit 90 / LTC 90 / 190 / MARK 10EX / 40	iLD 780	IR		31,0	35,5	40,0							x30,5m	600BD			
Linotronic MARK 40EX	iLD 780	IR		31,0	35,5	40,0							x60m	600BD			
Quicksetter 400 DRY	iLD 780	IR		25,0	31,0	33,8	35,5	40,6					x60m	600BD			
Hyphen																	
Spectraset 4200	LED 660	LDD	LDD	35,5									x60m				610CDH
Spectraset 4400	LED 660	LDD	LDD	66,0									x60m				610CDH
Spectraset 4800	iLD 780	IR		55,8	61,0	66,0	71,1	81,3					x60m				610CDH
Spectraset 3100	HeNe 633	HNS/ HNm	HND/ I-FRM		25,4	33,8	40,6						x60m/ x76,25m	600BD			
Spectraset 3200	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8	40,6	66,0							x76,25m	600BD			
Spectraset 2800	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	35,5	46,0							x60m	600BD			
Spectraset 3420	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8	40,6	52,0							x60m	600BD			
Spectraset 2400	LDR 670	HNS/ HNm	HND/ I-FRM	25,4	30,5	33,8	35,5						x60m/ x76,25m	600BD			
Spectraset 3320	LDR 650	HNS/ HNm	HND/ I-FRM		25,4	33,8	35,5						x60m/ x76,25m	600BD			
Spectraset 3325	LDR 650	HNS/ HNm	HND/ I-FRM		25,4	30,5	33,8	35,5	40,6	45,7	46,0		x60m/ x76,25m	600BD			
Dash V300	LDR 670	HNS		30,5	31,0								x30m				600D
Dash V400	LDR 670	HNS		31,0	40,0								x30m	600BD			
Dash 72 / 72 EQ / E-3000	iLD 780	IR		30,5	31,0								x30,5m				600D
Dash 94 / 94 EQ / 4-4000	iLD 780	IR		31,0	40,0								x30,5m	600BD			
Spectraset 1100	iLD 780	IR		20,3	30,5	33,8							x30,5m				600D
Spectraset 2100 / 2200	iLD 780	IR		25,4	30,5	33,8							x60m	600BD			
Spectraset 2300	iLD 780	IR		30,5	33,8								x30,5m	600BD			
Spectraset 3000	iLD 780	IR		33,8									x30,5m	600BD			
ICG																	
Itek 120-S	Ar488	AR (depleted)															42.6x58.6
Itek Laser Recorder 400R / 410R	Ar488	AR (depleted)		106,6									x60m	610CD			50.8x71.2
		AR (depleted)															71.2x106.8
Itek LED 220-S	LED 660	LDD	LDD														42.6x58.6

Itek LED Recorder 420R / 440RS / 444R	LED 660	LDD	LDD	106,6										x60m	610CD			50.8x71.1
		LDD	LDD															72.4x106.6
Titan 582	YAG 532	AR (depleted)		82,2										x60m	600CD			
ICG 430 R	HeNe 633	HNS		30,5	31,0									x30m	600BD			
ICG 455 R	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8	40,6	52,0								x60m	600BD			
ICG 435 R	iLD 780	IR		31,0	35,5	46,0								x60m	600BD			
Konica GRAPHIC IMAGING																		
EV-jetsetter 1100	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0									x30m	600BD			
EV-jetsetter 2000 / 2000 T	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	35,5								x60m	600BD			
EV-jetsetter 3100 / 3100T / 3100H / 3100S /	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	33,8	35,5							x60m/ x76,25m	600BD			
EV-jetsetter 5100 / 5100T / 5100H / 5100S /	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	33,8	35,5	36,8	40,6	45,7	46,0			x60m/ x76,25m	600BD			
EV-jetsetter 4100 / 4100 T	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	35,5	46,0							x60m	600BD			
EV-jetsetter 4500 / 4500 PRF	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	33,8	35,5	36,8	40,6	45,7	46,0			x60m/ x76,25m	600BD			
EV-jetsetter 6200	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	31,0	33,8	35,5	36,8	40,6	45,7	46,0			x60m/ x76,25m	600BD			
EV-jetsetter 6100	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	33,8	35,5	36,8	40,6	45,7	46,0			x60m/ x76,25m	600BD			
EV-jetsetter 7100	LDR 670	HNS/ HNm	HND/ I-FRM	35,5	40,6	45,7	46,0	47,0	50,8	51,0	52,0			x60m/ x76,25m	600BD			
EV-jetsetter 5500	LDR 670	HNS/ HNm	HND/ I-FRM	35,5	40,6	45,0	45,7	46,0	50,8	51,0	52,0	55,9		x60m/ x76,25m	600BD			
EV-jetsetter 8100	LDR 670	HNS/ HNm	HND/ I-FRM	35,5	40,6	45,7	50,8	53,0	55,9	61,0	62,5	63,5		x60m/ x76,25m	600BD			
EV-jetsetter 9100	HeNe 633	HNS/ HNm	HND/ I-FRM	35,5	40,6	45,7	50,8	53,0	55,9	61,0	62,5	63,5		x60m/ x76,25m	600BD			
EV-Jetsetter 9200	HeNe 633	HNS/ HNm	HND/ I-FRM	46,0	48,0	49,0	52,0	55,0	55,9	60,0	61,0	63,5		x60m/ x76,25m		610CDH		
		HNS/ HNm	HND/ I-FRM	45,7	47,2	49,8	50,8	61,0	63,5						610BD			
EV-jetsetter 1000	iLD 780	IR		30,5	31,0									x30,5m	600BD			
EV-jetsetter 2000 / 2000T	iLD 780	IR		30,5	31,0	35,5								x60m	600BD			
EV-jetsetter 4000 / 4000T	iLD 780	IR		30,5	31,0	35,5	46,0							x60m	600BD			
EV-jetsetter 3000 / 3000T	iLD 780	IR		30,5	33,8	35,5								x60m	600BD			
EV-jetsetter 5000 / 5000T	iLD 780	IR		30,5	33,8	35,5	40,6	46,0						x60m	600BD			
LaserGraph																		
LG-1 LaserGraph / LaserGraph LG-2	HeNe 633	HNm	I-FRM / I-FR7M															50.3x60.0
LG-2512 LaserGraph Quattro / Quattro-HS	HeNe 633	HNm	I-FRM / I-FR7M															53.3x66.3
	LDR 670	HNm	I-FRM / I-FR7M															48.0x66.3
LG-2523 LaserGraph ColorPlus-HS	LDR 670	HNS/ HNm	HND/ I-FRM	46,0										x60m	610CD			
LG-2524 LaserGraph Coroll-A	LDR 670	HNS/ HNm	HND/ I-FRM	33,0	35,6	38,1	40,6	43,0	45,7	46,0				x60m	610CD			
LG-2534 LaserGraph Coroll-B	LDR 670	HNS/ HNm	HND/ I-FRM	46,0	47,2	50,8	53,0	55,9	66,0	73,7	74,9	76,2		x60m	610CD			
Matsushita (MGCS)																		
AD/SAT 503-LD II	LED 660	LDD	LDD															38.0x58.4

MIT System															
FOTOPLOTTER MBA 140	LDR 650	HNS/ HNm	HND/ I-FRM / I-FR7M	55,0	76,2	107,9							x60m		610CDH
FOTOPLOTTER MBA 170	LDR 650	HNS/ HNm	HND/ I-FRM / I-FR7M	76,2	107,9	135,0							x60m		610CDH
Monotype Systems (iPA)															
ImageMaster 8500 / FuturoNews	HeNe 633	HNS/ HNm	HND/ I-FRM	40,0	43,0	46,0	52,0	55,0	61,0	67,0			x60m		610CDH
ImageMaster 9000	HeNe 633	HNS/ HNm	HND/ I-FRM	46,0	55,0	61,0	67,0	76,2	81,2	102,5	107,9		x60m		610CDH
Imagemaster 8000	HeNe 633	HNS/ HNm	HND/ I-FRM	104,0									x50m		600CD
	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8	52,0								x60m		600BD
CheckMaster / Pioneer 108 pica	HeNe 633	HNS/ HNm	HND/ I-FRM	25,0	31,0	35,5	43,0	46,0					x60m		600BD
ExpressMaster 1016 / 1270	HeNe 633	HNS/ HNm	HND/ I-FRM	25,0	30,5	35,5	43,0	46,0					x60m		600BD
Lasercomp 82e / Express 82	HeNe 633	HNS/ HNm	HND/ I-FRM	25,0	30,5	31,0	35,5						x60m/ x76,25m		600BD
Lasercomp 100/ 100 i / Express	HeNe 633	HNS/ HNm	HND/ I-FRM	25,0	30,5	31,0	35,5	43,0					x60m		600BD
ExpressMaster 1000 / NewsExpress82pica	HeNe 633	HNS/ HNm	HND/ I-FRM	25,0	31,0	35,5							x60m/ x76,25m		600BD
ExpressMaster 1200 / NewsExpress 108pica	HeNe 633	HNS/ HNm	HND/ I-FRM	25,0	31,0	35,5	40,6	43,0	46,0				x60m		600BD
ImageMaster 3000/1524	HeNe 633	HNS		30,5	31,0								x30m		600BD
Lasercomp. 70/70 i / Pioneer, Balsler / Sprint	HeNe 633	HNS		20,3	25,4	30,5							x30m		600D
ImageMaster 4000	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8									x60m		600BD
ImageMaster 5000	HeNe 633	HNS/ HNm	HND/ I-FRM		25,4	33,8	40,6						x60m/ x76,25m		600BD
ImageMaster 6000 / ExpressMaster 6000	HeNe 633	HNS/ HNm	HND/ I-FRM	31,0	35,5	43,0	52,0						x60m		600BD
ImageMaster 7000	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8	40,6	66,0							x76,25m		600BD
ECRM VRL45 / VRL 45HS	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	35,5	46,0						x60m		600BD
ImageMaster 1000 / 1500	LDR 670	HNS/ HNm	HND/ I-FRM	25,4	30,5	33,8	35,5						x60m/ x76,25m		600BD
ExpressMaster 3850	LDR 670	HNS/ HNm	HND/ I-FRM	25,0	35,5	35,5	38,1	40,0	44,0				x60m/ x76,25m		610BD
ExpressMaster 20	LDR 650	HNS/ HNm	HND/ I-FRM		25,4	30,5	33,8	35,5					x60m/ x76,25m		600BD
ExpressMaster 25	LDR 650	HNS/ HNm	HND/ I-FRM		25,4	30,5	33,8	35,5	40,6	45,7	46,0		x60m/ x76,25m		600BD
ExpressMaster 4550	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	31,0	33,8	35,5	36,8	40,6	45,7	46,0		x60m/ x76,25m		600BD
Panther / PantherPro	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	33,8								x60m/ x76,25m		600BD
Ultara 36	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	33,8	35,5	38,1						x60m/ x76,25m		600BD
Catara 46	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	33,8	35,5	40,6	45,7	46,0				x60m/ x76,25m		600BD
Pantara 62	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	33,8	35,5	38,1	40,6	45,7	46,0	50,8	62,5	x60m/ x76,25m		600BD
ECRM VR-45 / VR-45HS	iLD 780	IR		30,5	31,0	35,5	46,0						x60m		600BD
Ultre 72EQ	iLD 780	IR		30,5	31,0								x30,5m		600D
Ultre 3000	iLD 780	IR		31,0									x60m#30m		600BD
Ultre 4000	iLD 780	IR		31,0	35,5	40,0							x60m#30m		600BD
Prism/Prism Plus	iLD 780	IR		20,3	30,5	31,0							x30m		600D
ImageMaster 2000	iLD 780	IR		30,5	31,0								x30m		600D

Eclipse	iLD 780	IR		30,5	33,8									x30m	600BD			
Optronic																		
ColorSetter 2000 / 4000 / 4200 / 4400	Ar 488	AR (depleted)																50.8x66.0
ColorSetter XL 2000 / XL 4000	Ar 488	AR (depleted)																104.1x132.1
PlateSetter Aurora	Ar 488	AR (depleted)																56.0x67.0
	YAG 532	AR (depleted)																90.1x113.0
DeskSetter 3000 / Express	iLD 780	IR		33,8										x30m	600BD			
Orbotech																		
SPrint 110 / 120 / 120 N / 220	iLD 780	IR																76.2x81.3
	iLD 780	IR																81.2x101.1
P.D.I. / Isomet																		
P.D.I. 255 / 355 / 455 SMO / LMO	Ar 488	AR (depleted)																50.8x61.0
P.D.I. 455 JMO	Ar 488	AR (depleted)																76.2x101.6
PrePRESS Solutions (IPA)																		
Varityper VT 5660 E	HeNe 633	HNS/ HNm	HND/ I-FRM	38,1										x60m	610CD			
Varityper VT 5860 E	HeNe 633	HNS/ HNm	HND/ I-FRM	66,0										x60m	610CD			
Varityper VT 5960 E	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	50,8	76,2	83,8							x60m	600CD			
AM Varityper VT 5330 / 5320 / 5310	HeNe 633	HNS		30,5	31,0									x30m	600BD			
AM Varityper VT 5500	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	35,5	43,0	46,0							x60m	600BD			
Varityper VT 5630	HeNe 633	HNS/ HNm	HND/ I-FRM		25,4	33,8	40,6							x60m/ x76,25m	600BD			
Varityper VT 5830	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8	40,6	66,0								x76,25m	600BD			
PantherPlus 52	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	33,8	35,5	38,1	40,6	45,7	46,0	50,8	53,0		x60m/ x76,25m	600BD			
PantherPro 62 / Pantara 62	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	33,8	35,5	38,1	40,6	45,7	46,0	50,8	62,5		x60m/ x76,25m	600BD			
PantherPro 46 / PantherPlus 46 Catara 46	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	33,8	35,5	40,6	45,7	46,0					x60m/ x76,25m	600BD			
VT 5300 W	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	33,8	35,5	40,6	45,7	46,0					x60m/ x76,25m	600BD			
PantherPlus / Panther / PantherPro	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	33,8									x60m/ x76,25m	600BD			
VT 5300 H	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	33,8									x60m/ x76,25m	600BD			
PantherPro 36 / PantherPlus 36 / Ultara 36	LDR 670	HNS/ HNm	HND/ I-FRM	30,5	33,8	35,5	35,5	38,1						x60m/ x76,25m	600BD			
VT4200 / 4300 / 5000 / 5300E / 5324	iLD 780	IR		30,5										x30m	600BD			
VT 5300E / VT 4990 / VT 6000 / VT 3990	iLD 780	IR		30,5	33,8									x60m	600BD			
VT 5300H / VT 5300B / VT 6990	iLD 780	IR		30,5	33,8									x60m	600BD			
Panther Plus / Panther	iLD 780	IR		30,5	33,8									x60m	600BD			

Purup-Eskofot / (Esko-Graphics)																
Purup PE 2000 / PE 3000	Ar 488	AR (depleted)														43.1x43.1
Purup PE 4000/ 5000 / 5100	Ar 488	AR (depleted)														63.5x63.5
Purup PE 7000 / 7100 / 9000	Ar 488	AR (depleted)		38,0	50,8	63,5								x60m	600CD	63.5x63.5
ImageMaker PIM-80/10 / PIM-80/20	Ar 488	AR (depleted)		25,0	34,0	43,0	53,0							x60m		600CDH
ImageMaker PIM-80/10 / PIM-80/20	iLD 780	IR		25,0	34,0	43,0	53,0							x60m		600CDH
ImageMaker PIM-80/15	Ar 488	AR (depleted)		25,0	34,0	37,9	43,0							x60m		600CDH
ImageMaker PIM-80/15	iLD 780	IR		25,0	34,0	38,0	43,0							x60m		600CDH
ImageMaker PIM-80/05	Ar 488	AR (depleted)		35,6										x60m		600CDH
ImageMaker PIM-80/05	iLD 780	IR		35,6										x60m		600CDH
Maestro / Maestro-RS	Ar 488	AR (depleted)		25,0	34,0	43,0	53,0	55,0						x60m		600CDH
Maestro / Maestro-RS	HeNe 633	HNS/ HNm	HND/ I-FRM	25,4	34,0	43,0	53,0	54,9						x60m		600CDH
Maestro / Maestro-RS / Maestro-NP	iLD 780	IR		25,0	34,0	43,0	53,0	55,0						x60m		600CDH
Maverick	iLD 780	IR		25,0	34,0	40,6	43,0	53,0						x60m		600CDH
MAGNUM-Classic / MAGNUM-Medley	Ar 488	AR (depleted)		43,0	53,0	55,0	71,9	76,2	81,2	82,0				x60m		600CDH
MAGNUM-Classic / MAGNUM-Medley	HeNe 633	HNS/ HNm	HND/ I-FRM	43,0	45,7	54,9	55,9	61,0	71,9	76,2	81,3	82,0		x60m		600CDH
MAGNUM-Classic / MAGNUM-Medley	iLD 780	IR		43,0	53,0	55,0	71,9	76,2	81,3	82,0				x60m		600CDH
MAGNUM-RS / MAGNUM-Mercur	Ar 488	AR (depleted)		40,6	43,0	55,0	62,0							x60m		600CDH
MAGNUM-RS / MAGNUM-Mercur	HeNe 633	HNS/ HNm	HND/ I-FRM	40,6	43,0	45,7	54,9	55,9	61,0	62,0				x60m		600CDH
MAGNUM-RS / MAGNUM-Mercur	iLD 780	IR		40,6	43,0	55,0	62,0							x60m		600CDH
PlateSetter MERLIN	Ar 488	AR (depleted)		43,0	53,0	55,0	71,9	76,2	81,2	82,0				x60m		600CDH
MAGNUM B1 Ctf / MAGNUM B1 Ctf-HS	Ar 488	AR (depleted)		35,6	53,0	55,0	71,9	76,2	81,2	82,0				x60m		600CDH
MAGNUM B1 Ctf / MAGNUM B1 Ctf-HS	HeNe 633	HNS/ HNm	HND/ I-FRM	35,6	45,7	53,0	54,9	55,9	71,9	76,2	81,3	82,0		x60m		600CDH
MAGNUM B2 Ctf / MAGNUM B2 Ctf-HS	Ar 488	AR (depleted)		35,6	43,0	46,0	50,8	53,0	55,0	62,0				x60m		600CDH
MAGNUM B2 Ctf / MAGNUM B2 Ctf-HS	HeNe 633	HNS/ HNm	HND/ I-FRM	35,6	43,0	45,7	50,8	53,0	54,9	55,9	61,0	62,0		x60m		600CDH
DPX-5080	LDR 670	HNS/ HNm	HND/ I-FRM	35,6										x76,25m	610BD	
DPX-5080	LDR 670	HNS/ HNm	HND/ I-FRM	35,6										x60m	610CD	
ImageMaker MARVEL / DPX Genesis	iLD 760	IR		31,0										x30m		600D
Scangraphic PrePress Techn. (iPA)																
Scantext Futuro HN	HeNe 633	HNS/ HNm	HND/ I-FRM	40,0	43,0	46,0	52,0	55,0	61,0	67,0				x60m		610CDH
Scantext Futuro News	HeNe 633	HNS/ HNm	HND/ I-FRM	40,0	43,0	46,0	52,0	55,0	61,0					x60m		610CDH
Scantext Largo	HeNe 633	HNS/ HNm	HND/ I-FRM	104,0										x50m	600CD	
		HNS/ HNm	HND/ I-FRM	33,8	52,0									x60m	600BD	
Scantext 2030 Laser	HeNe 633	HNS/ HNm	HND/ I-FRM	25,0	30,5	31,0								x60m	600BD	
Scantext 2051 Laser	HeNe 633	HNS/ HNm	HND/ I-FRM	31,0	35,5	45,0	51,0	52,0						x60m	600BD	
Scantext 2030 / ChromaSpeed 2032	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8										x60m	600BD	
Scantext Tempo / Rondo 338	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8										x60m	600BD	

Scantext 2052 ChromaSpeed	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8	52,0									x60m	600BD			
Scantext Tempo (Plus) / Rondo (Plus)	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8	52,0									x60m	600BD			
Scantext OTHELLO / OTHELLO S	HeNe 633	HNS/ HNm	HND/ I-FRM	33,8	40,6	52,0								x60m	600BD			
Scantext Rondo 406	HeNe 633	HNS/ HNm	HND/ I-FRM	40,6										x60m	600BD			
Scantext ExpressMaster	HeNe 633	HNS/ HNm	HND/ I-FRM	31,0	35,5	43,0	52,0							x60m	600BD			
Scantext 2030 PD / ColorStar / Primo	iLD 780	IR		33,8										x60m	600BD			
Scantext 2051 PD / Janus PD	iLD 780	IR		33,8	52,0									x50m	600BD			
Scanview / (Esko-Graphics)																		
DotMate 6500P	LDR 670	HNS/ HNm	HND/ I-FRM	33,9	37,0	40,0	43,0	46,0	48,0					x60m		610CDH		
DotMate 7500SA Plus / 7500P Plus	LDR 670	HNS/ HNm	HND/ I-FRM	40,0	43,0	46,0	49,0	52,0	55,0	58,0	61,0			x60m		610CDH		
Dotmate 7500P / 7500SA	LDR 670	HNS/ HNm	HND/ I-FRM	40,0	43,0	46,0	49,0	52,0	55,0					x60m		610CDH		
DotMate 4000 / 4900	LDR 670	HNS/ HNm	HND/ I-FRM	35,5										x60m	610BD			
DotMate 5000 P / 5000 SA / 5000 CTP	LDR 670	HNS/ HNm	HND/ I-FRM	25,0	25,4	30,5	33,8	35,5	40,6	42,0				x60m/ x76,25m	600BD			
Scitex																		
ELP III-Plotter	Ar 488	AR (depleted)		76,2	106,6									x60m	610CD			
ERAY-Plotter	Ar 488	AR (depleted)		91,4	111,7									x60m	610CD			84.7x105.9
Raystar Laser-Plotter	Ar 488	AR (depleted)		50,8										x60m	610CD			
Dolev 100 200 / 250	HeNe 633	HNS/ HNm	HND/ I-FRM	38,1										x60m	610CD			
Dolev 400 PSI / 440 / 440F / 450 / 450F	HeNe 633	HNS/ HNm	HND/ I-FRM	66,0										x60m	610CD			
Dolev 800 HeNe 633	LDR 650	HNS/ HNm	HND/ I-FRM	30,5	50,8	76,2	83,8							x60m	600CD			
Dolev 800V / 800V2 / 800E / 800V3 / 800V4	LDR 650	HNS/ HNm	HND/ I-FRM	30,5	50,8	76,2	83,8	86,3						x60m	600CD			
Dolev 800 LF	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	35,5	40,6	45,7	50,8	55,9	66,0				x60m	600CD			
Dolev 4press / 4pressV / 4press VXL	LDR 650	HNS/ HNm	HND/ I-FRM	35,6	38,1	50,8	55,9	66,0	73,7	74,9	76,2	81,2		x60m	610CD			
Dolev 4news / 4newsV / 4newsVXL	LDR 650	HNS/ HNm	HND/ I-FRM	35,6	38,1	50,8	55,9	66,0	73,7	74,9	76,2	81,2		x60m	610CD			
Dolev 2pressPlus	LDR 650	HNS/ HNm	HND/ I-FRM	25,4	30,5	38,1	40,6	55,9						x60m	610CD			
Rimon 44/55	LDR 635	HNS	HND/ I-FRM	66,0	76,2	81,3	83,8	127,0						x60m	600CD			
Rimon 50/66	LDR 635	HNS	HND/ I-FRM	66,0	76,2	81,3	83,8	127,0						x60m	600CD			
Dolev 2DRY	iLD 780			30,5	35,5	40,6												
Dolev 4DRY	iLD 780			35,5	38,0	50,8	55,8	66,0	73,7	74,9								
Screen																		
Scanagraph SG-608 / 608 II	HeNe 633	HNS/ HNm	HND/ I-FRM / I-FR7M	66,0										x60m	610CD			53.0x66.0
Scanagraph SG-688	HeNe 633	HNS/ HNm	HND/ I-FRM / I-FR7M	66,0	101,6									x60m	610CD			66.0x101.6
Scanagraph SG-737 / SG-747	HeNe 633	HNS/ HNm	HND/ I-FRM / I-FR7M															61.0x81.3
Scanagraph SG-618	HeNe 633	HNS/ HNm	HND/ I-FRM	50,8	66,0									x60m	610CD			
Scanica SF-222 / SF-323	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5										x60m	610CD			
Scanica SF-123	HeNe 633	HNS/ HNm	HND/ I-FRM	25,4										x60m	610CD			

Scanagaph SG-808 II / SG-708	Ar488	AR (depleted)																55.0x76.5
Scanagraph SG-818	Ar488	AR (depleted)		53,0	66,0								x60m	610CD				53.3x66.3
Scanagraph SG-888	Ar488	AR (depleted)		66,0									x60m	610CD				66.0x101.6
Scanagraph SG-757	Ar488	AR (depleted)		40,6	81,3								x60m	610CD				
Scanagaph SG-777	Ar488	AR (depleted)		61,0	121,9								x60m	610CD				
Scanagraph SG-111	LED 660	LDD	LDD															55.0x63.5
ImageSetter DT-R 1035 / DT-R 2035	LED 660	LDD	LDD	35,5									x60m		610CDH			
ImageSetter DT-R 1065 / DT-R 2065	LED 660	LDD	LDD	66,0									x60m		610CDH			
Scanagraph SG-717	iLD 780	IR																53.0x66.0
ImageSetter FT-R 1035	iLD 780	IR		20,3	25,4	30,5	35,5						x60m		610CDH			
ImageSetter FT-R 1050 / SF-2050 R	iLD 780	IR		20,3	25,4	30,5	35,5	40,6	45,7	50,8			x60m		610CDH			
ImageSetter / Recorder MT-R 1080	iLD 780	IR		66,0									x60m		610CDH			
ImageSetter / Recorder MT-R 1100	iLD 780	IR		71,1									x60m		610CDH			
ImageSetter / Recorder MT-R 1120	iLD 780	IR		55,8	61,0	66,0	71,1	81,3					x60m		610CDH			
ImageSetter / Recorder MT-R 1120P	iLD 780	IR		83,8									x60m		610CDH			
Capstan Film Recorder FT-R 3035	LDR 635	HNS/ HNm	HND/ I-FRM	25,4	30,5	35,5	40,6						x60m		600CDH			
Capstan Film Recorder FT-R 3050	LDR 635	HNS/ HNm	HND/ I-FRM	35,5	40,6	45,7	50,8	55,9					x60m		600CDH			
ImageSetter DT-R 3075	LED 660	LDD		40,6	66,0	76,2							x60m		610CDH			
ImageSetter DT-R 3100	iLD 780	IR		50,8	61,0	66,0	71,1	76,2	81,3				x60m		610CDH			
Katana FT-R 5040	LDR 635	HNS/ HNm	HND/ I-FRM	25,4	30,5	35,5	40,6						x60m		600CDH			
Katana FT-R 5055	LDR 635	HNS/ HNm	HND/ I-FRM	30,5	35,5	40,6	45,7	50,8	55,9	61,0			x60m		600CDH			
DT-R 5120 Tanto	LED 660	LDD	LDD	61,0	66,0	71,1	80,0	83,8					x60m		610CDH			
DT-R 6120 Tanto	LED 660	LDD	LDD	61,0	66,0	71,1	80,0	83,8					x60m		610CDH			
CT-R 80 S	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	35,5								x60m		600BD			
CT-R 108 CS	HeNe 633	HNS/ HNm	HND/ I-FRM	30,5	35,5	46,0							x60m		600BD			
Desktop Colour Recorder DC-R 1030	iLD 780	IR		33,8									x30m		600BD			
Secma International / CTM																		
SWIFTLine Imagesetter 2026	LDR 635	HNm /	I-FRM / IFR7m															52.1x64.8
SWIFTLine Imagesetter 2636	LDR 635	HNm /	I-FRM / IFR7m															66.0x91.4
SWIFTLine Imagesetter 4247	LDR 635		I-FR7M															106.6x120.0
SWIFTLine Imagesetter 4763	LDR 635		I-FR7M															120.0x161.2
Strobbe																		
Strobbe CE 55	LDR 670	HNS/ HNm	HND/ I-FRM	41,2									x60m		600CD			
Ultre Corp.																		
UltreSetter 4800	HeNe 633	HNS/ HNm	HND/ I-FRM	25,0	31,0	46,0	51,0						x60m		600BD			

UltreSetter 5800	LDR 670	HNS/HNm	HND/ I-FRM	25,0	31,0	33,8	35,5	40,6	46,0				x60#30m	600BD			
UltreSetter 5400	LDR 670	HNS/HNm	HND/ I-FRM	25,0	31,0	33,8	35,5	40,6					x60#30m	600BD			
Ultre Vision 300	LDR 670	HNS		30,5	31,0								x30m	600BD		600D	
Ultre Vision 400	LDR 670	HNS		30,5	31,0	40,0							x30m	600BD			
UltreSetter 72 / 72E / 72P	iLD 780	IR		30,5	31,0								x30m			600D	
UltreSetter 94 / 94E	iLD 780	IR		31,0	35,5	40,0							x60#30m	600BD			
UltreSetter 3000	iLD 780	IR		31,0									x60#30m	600BD		600D	
UltreSetter 4000	iLD 780	IR		31,0	35,5	40,0							x60#30m	600BD		600D	
UltreSetter 5400 dry	iLD 780	IR		30,5	31,0	33,8	35,5	40,6					x60#30m	600BD			

TEXTILES - SCANNER - PLOTTER

CST																	
CST-drum-film plotter	iLD 820	IR		76,2	85,0	101,6	106,6	111,7	120,0	122,0			x60m	610C			
Robustelli																	
RobLaser SP 1100	iLD 780	IR		76,2	85,0	101,6	106,6	111,7	120,0	122,0			x60m	610C			
Stork																	
STK-2000 / 3000 / CSP 3001	iLD 780	IR		76,2	106,6	118,0							x60m	610C			
Lüscher																	
Lüscher 220 PageSetter / 2012	LED 660	LDD	LDD	106,6	109,2			76,2	111,7	121,9			x60m	610C	600C		122.0x220.0
Lüscher 160 PageSetter	LED 660	LDD	LDD	106,6	109,2			76,2	111,7	121,9			x60m	610C	600C		122.0x160.0
Lüscher 120 PageSetter	LED 660	LDD	LDD	106,6	109,2			76,2	111,7	121,9			x60m	610C	600C		120.0x122.0