



"Even better than anticipated"

Super-Wide Digital (UK) has added Agfa's Jeti Tauro H3300 LED press to their huge stable of Super-Wide format machines.

Sign & Display News



Higher productivity at Interpack

The folding carton manufacturer has also seen its chemistry and water consumption lowered, while press conditions got more stable and restarts faster.

Packaging Printing News



Cut back your press' alcohol consumption

Use ANTURA fount AFS2 to reduce your sheet-fed press' IPA dosage to 2-3% or even 0% without a lot of extra effort.

Commercial Printing News



"We really print on anything"

A new Anapurna H3200i LED boasts Unfold's flexibility and efficiency in answering customer requests, while significantly reducing media waste.

Sign & Display News



Ensuring business continuity at all times

Manage prepress production on-site or from home with our secure cloud-based SaaS solution Arkitek Cloud, even in challenging circumstances.

Newspaper Printing News



Altamira Design PID

This new single-pass UV inkjet ink set is optimized for printed interior decoration, such as furniture edge bands, profiles, and panels.

Industrial Printing News