



**Studio 4D48**

Watch the sessions from our recent virtual event to discover how you can benefit from our latest made-to-measure offset printing innovations.

All Studio 4D48 News



**Oberon RTR3300 demo**

See this dedicated 3.3 m high-end roll-to-roll inkjet printer in action in a live demo recording from our headquarter showroom in Belgium.

All Sign & Display News



**Enhanced quality and eco-friendliness**

Apogee, PressTune and InkTune helped Swedish printer TMG streamline print production, improve quality and reduce ink consumption by 20%.

All Commercial Printing News



**Increased inkjet ink production capacity**

We invest in a new manufacturing plant that will focus on water-based inkjet inks for laminate flooring and furniture, as well as corrugated packaging.

All Industrial Printing News

**New products and services announced at Studio 4D48**



Second generation of **Adamas** chem-free printing plates delivers enhanced performance and eco-friendliness



**Plate loading robot** streamlines and speeds up prepress operations, while reducing the overall cost.



New **Energy Verve** pre-heat printing plate combines cost efficiency with high performance.



**Apogee v12 workflow software** delivers increased automation and smooth customer interaction.



New **PrintSphere Disaster Recovery** service secures newspaper printers' daily print production.



**Arkitex Production v4.0** takes the next step in streamlining and automating newspaper print production workflows.