

Studio 5D10

Our virtual event took place last week but you can still view the broadcasts covering our latest innovations in inkjet printing – for sign & display as well as industrial printing applications.



Growing and diversifying your business – Wide-format inkjet for offset printers



From flat to finish – Corrugated inkjet printing



Going the extra mile – Syncing inkjet components for a perfect print result

[View the recordings](#)



New Jeti Tauro H3300 S LED

This favorably priced and upgradable entry model will enable even more printing companies to benefit from one of our flagship large-format printers.

All Sign & Display News



A more stable production flow

Danish printer KLS PurePrint achieved a smooth and eco-friendly prepress production flow with Agfa's Adamas plate and Apogee software.

All Commercial Printing News



IJ for high-performing Agfa UV inks

"If the ink is not reliable, nothing I can do with the machine is going to fix that" says John Corral, MD of system builder Industrial Inkjet Ltd.

All Industrial Printing News



Further reducing maintenance in prepress

For newspaper printing companies the new Attiro Cleaning Module limits the number of cleaning interventions to three or maximum four per year.

All Newspaper News



Oberon RTR3300

2020 Product of the Year in the class of Roll-to-Roll UV printers over 80 inches



2020 Product of the Year in the class of UV Hybrid/Flatbed High Volume Production printers



Jeti Tauro H3300 LED