



**MIS-Workflow integration webinar**

Only 1 day to go... Have you registered yet for the March 11 Agfa & Dataline broadcast on improving efficiency thanks to MIS-workflow integration?

*All Commercial Printing News*



**New Jeti Tauro H3300 UHS LED**

Our fastest inkjet printer yet prints 24/7 at speeds up to 600 m<sup>2</sup>/h. Next to large-format prints, it can also handle corrugated cardboard printing and packaging.

*All Sign & Display News*

*All Packaging Printing News*



**Increasing output capacity by 2.5 times**

With its new Jeti Tauro H3300 LED printer, ColorDynamics will meet its goal of delivering high-quality prints faster, direct-to-store.

*All Sign & Display News*



**FuturePrint talk on printing décor paper**

At this virtual conference Marc Graindourze discussed the role of inkjet printing for laminated surfaces, such as floors and furniture panels.

*All Industrial Printing News*