



ANILOX CLEANER SD

Auto Machine Anilox Detergent

DESCRIPTION:

Anilox Cleaner SD is formulated to quickly clean water-based, UV and solvent based inks both manual and cleaning machinery applications. The product will penetrate deeply into the anilox cells to clean dried ink and sequester it so it will not re-deposit during the cleaning process. This is an aggressive, highly alkaline anilox roller cleaner and should not be used where soft metals are present.

DIRECTIONS FOR USE:

Flexographic Ink Cleaning: Apply full strength or dilute with water up to 50% to clean water-based conventional, solvent and UV flexographic ink.

Hot Tank or Ultrasonic Units: Mix with up to 90% water. Set tank temperature to a maximum of 140 degrees F. **READ MSDS BEFORE USE. DO NOT ALLOW PRODUCT TO FREEZE. AVOID CONTACT WITH SOFT METALS LIKE ALUMINUM. CORROSIVE LIQUID.**

FEATURES AND BENEFITS:

- * Strong, Water-Based Concentrate.
- * Cleans anilox rollers, rubber rolls, Ink Pans and Floors.
- * Low odor and non-flammable and zero VOC product.
- * Will not damage photopolymer materials.

SPECIFICATIONS:

Flashpoint: None

VOC: None Odor: Detergent

pH: 12.5-13.0 (Concentrate)

Appearance: Translucent Water Based Mixture

Drying Speed: Not Applicable

HMIS RATING:

Health: 2 Flammability: 0 Reactivity: 0 Personal Protection: B

PACKAGING:

5 gallon pails, 55 gallon drums

Pitman Company
611 River Drive * Center 3
Elmwood Park, NJ 07407
Phone: 888-274-8626 shop.agfagraphics.us