



## Technical Data Sheet

### MRC 100

#### ULTRA FAST DRYING, 100 GRAM/LITER METERING ROLLER CLEANER

#### DESCRIPTION:

MRC 100 is an ultra- fast drying Metering Roller Cleaner formulated to meet the requirements of 100 grams per liter as legislated by SCAQMD. This product is only intended to be used as a metering roller cleaner and not a roller and blanket wash.

#### DIRECTIONS FOR USE:

Apply full strength at room temperature. Flammable liquid. Keep away from heat and open flame. Store and use in a well ventilated area. For use as a metering roller cleaner only.

**READ MSDS BEFORE USE.**

#### FEATURES AND BENEFITS:

- \*Very fast drying
- \*No residue cleaner.
- \*Excellent non-chlorinated metering roller cleaner.
- \*Low VOC by SCAQMD 1171 standards at 92 grams per liter.

#### SPECIFICATIONS:

Flashpoint: 0 degrees F  
VOC=s: 0.8 lb/gal (92 grams/liter) 12% acetone exempt  
Drying Speed: Very fast  
Cleaning Strength: Very Strong  
Odor: Strong Solvent  
Composite Vapor Pressure (mmHG): 63.4

#### HMIS RATING:

Health: 2 Flammability: 3 Reactivity: 0 Personal Protection: B

#### PACKAGING:

5 gallon pails, 55 gallon drums