



Technical Data Sheet

MRC 2010

LOW VAPOR PRESSURE, FAST DRYING METERING ROLLER CLEANER

DESCRIPTION:

MRC 2010 is a fast drying solvent blend formulated to clean metering rollers in continuous dampening systems. The product is considered a low vapor pressure product with a composite vapor pressure under 10mm HG. This product will clean quickly and leave no residue. It can also be used to clean back cylinders and used as a fast drying typewash.

DIRECTIONS FOR USE:

For Metering Rollers: Disengage metering roller from contact with other rollers. Apply full strength using a saturated cloth. Metering rollers should be cleaned daily or whenever a build-up appears.

FLAMMABLE LIQUID. READ MSDS BEFORE USE.

FEATURES AND BENEFITS:

- * Low Vapor Pressure product
- * Extremely effective metering roller cleaner
- * Fast drying speed
- * Leaves no oily residue
- * Cleans back cylinders

SPECIFICATIONS:

Flashpoint: Greater than 45 degrees F. TCC

VOC: 6.59 lb/gal (790 grams/liter), 100%

Drying Speed: Fast

Solvent Strength: Strong

Odor: Solvent

Composite Vapor Pressure (mmHG): 9.58 at 20 degrees F

HMIS RATING:

Health: 2 Flammability: 3 Reactivity: 0 Personal Protection: C

PACKAGING:

5 gallon pails and 55 gallon drums