



Technical Data Sheet

TOWER MRC

VERY FAST DRYING METERING ROLLER CLEANER

DESCRIPTION:

Tower MRC is a fast drying solvent blend formulated to clean metering rollers in continuous dampening systems. This product will clean quickly and leave no residue. It can also be used to clean back cylinders and used as a fast drying typewash.

DIRECTIONS FOR USE:

For Metering Rollers: Disengage metering roller from contact with other rollers. Apply full strength using a saturated cloth. Metering rollers should be cleaned daily or whenever a build-up appears.
FLAMMABLE LIQUID. READ MSDS BEFORE USE.

FEATURES AND BENEFITS:

- * Extremely effective metering roller cleaner
- * Very fast drying speed
- * Leaves no oily residue
- * Cleans back cylinders

SPECIFICATIONS:

Flashpoint: Less than 20 degrees F. TCC
VOC: 4.20 lb/gal (503 grams/liter), 84% acetone exempt
Drying Speed: Very fast
Solvent Strength: Strong
Odor: Solvent
Composite Vapor Pressure (mmHG): 25 at 68 degrees F

HMIS RATING:

Health: 2 Flammability: 3 Reactivity: 0 Personal Protection: B

PACKAGING:

4x1 gallon case and 55 gallon drums