



## Technical Data Sheet

### MRC-LV

#### LOW VOC METERING ROLLER CLEANER

#### DESCRIPTION:

MRC-LV is a very fast drying, low VOC metering roller cleaner. The product features great cleaning strength and no residue.

#### DIRECTIONS FOR USE:

Apply full strength at room temperature. Keep away from heat and open flame. Use in a well ventilated area.

**FLAMMABLE LIQUID. READ MSDS BEFORE USE.**

#### FEATURES AND BENEFITS:

- \*Very fast drying
- \*No residue cleaner.
- \*Excellent non-chlorinated metering roller cleaner.
- \*Low VOC Product to meet local regulations.
- \*Uses include metering roller cleaner and typewash.

#### SPECIFICATIONS:

Flashpoint: 18 degrees F  
VOC=s: 1.68 lb/gal (202 grams/liter) 26% acetone exempt  
Drying Speed: Very fast  
Cleaning Strength: Strong  
Odor: Solvent

#### HMIS RATING:

Health: 2 Flammability: 3 Reactivity: 0 Personal Protection: B

#### PACKAGING:

55 gallon drums