

COLEX

AUTOMATION SOLUTIONS

FOTOBA


New

YOU PRINT
WE CUT

NEW FOTOBA XL320

HIGH PERFORMANCE Automatic X/Y Cutting Rolls up to 130" Wide

- Faster Speeds
- Flexible Media up to 40 mil
- Cuts a wide range of Textile/Fabrics



**Wide Format Finishing
Just Got Easier...**

55-57 Bushes Lane • Elmwood Park, NJ 07407 • USA

P: (201) 265-5670 • F: (201) 265-7093 • E: sales@colex.com • www.colex.com

NEW FOTOBA XL320

THE NEW FOTOBA XL320 SUPER WIDE X/Y ROLL TO SHEET CUTTER

The **FOTOBA XL** series cutters are super fast to eliminate the bottlenecks in your finishing department. A single cutter is capable of handling the output of several printers. The XL cutters uses **FOTOBA CUTMARKS** to follow the edge of the image. Regardless of any feed misalignment, the XL Cutter will automatically realign itself to the edge of the printed image. The XL cutter will always produce square finished images even if the printer fails to print parallel to the media edge or if the printer fails to wind up the rolls squarely (telescoping).



FOTOBA CUT MARK

FOTOBA CUTMARKS are embedded in most popular RIP softwares.




The XL320 can cut a 150 foot Roll in under 10 minutes!

The XL Series can handle media with a maximum thickness of 40 mil including polycarbonate, laminates and encapsulated media, photo paper, vinyl, self-adhesive vinyl, graphic arts film, duratrans, canvas and much more.



Heavy Duty Roll Feeder



- Self squaring to the edge of the image (X)
- Automatic tracking to the image edge (Y)

FEATURES:

- | | |
|--|--|
| • Self squaring to the edge of the image (X) | • Memory channels to store different cut marks |
| • Automatic tracking to the image edge (Y) | • All mechanism controlled by stepper motors |
| • Max linear speed 50-ft per minute | • Automatic scanning of the cut marks |
| • Vertical Slitters: Single, 8mm double or adjustable double | • Self sharpening blade system |
| • Cutting by length & quantities for media conversion | • Accuracy + - 1mm (0.04 in.) X & Y |

Model	Max Roll Size Diameter	Max Paper Width (Inches)	Min Paper Width (Inches)	Net Weight (Lbs)	Dimensions Inches	Air Requirements	Electrical Requirements
XL320	10"	130"	43"	705 lbs	169" x 28" x 46"	60 psi, .25 cfm	110 V