

Technical Data Sheet

ORGACON IJ1005 ink

Water based inkjet ink for transparent conductive patterns

Agfa's ORGACON IJ1005 is a transparent conductive inkjet ink based on conductive PEDOT:PSS polymer. It can be applied with different piezo inkjet platforms on rigid and flexible substrates for applications like capacitive touch pads, membrane switches, smart packaging, printed sensors and hole injection layer of Organic Photovoltaics.

TYPICAL VALUES

Properties	Unit	Value	
SER @WCT 40µm on PET Dried @130°C/3min	Ohm/sq	75	
VLT @ WCT 40µm	%	>83	
Dimatix DMP-2831 test	SER	Ohm/sq	800
	VLT	%	96
Weight PEDOT:PSS	%	0,8	
Acidity	pH	2	
Viscosity @20°C, 100 1/s	mPas	9	
Surface tension	mN/m	34	
Shelf life from production date when stored between 4 and 25°C in sealed container	month	6	

PROCESSING GUIDELINES

Printer compatibility

ORGACON IJ1005 is successfully tested with different piezo inkjet platforms including Microdrop, Dimatix DMP-2800 and Spectra Galaxy 30.

Printing and curing

Air bubbles in inkjet ink should absolutely be avoided, as they would counteract the jetting of the ink. Therefore, filtration of the ink for insertion into the inkjet cartridge is not recommended. If it is nevertheless decided to filter in advance, this must be done carefully. Filters that can be used are hydrophilic types like 0,2µm syringe or 0,4µm glass fibre.

It is essential to degas the ink before use.

Print head settings and drying conditions will vary based on the users' application requirements and printing and drying equipment. Contact us at info.orgacon@agfa.com for platform-specific recommendations.

HEALTH AND SAFETY

Please check the Safety Data Sheet at msds.agfa.com .

CONTACT

For more information, please contact us via e-mail at conductivematerials@agfa.com or via www.agfa.com/conductivematerials .

© March 2023, Agfa-Gevaert N.V. - All rights reserved. Published by Agfa-Gevaert N.V. - B-2640 Mortsel, Belgium
ORGACON, Agfa and the Agfa rhombus are trademarks of Agfa-Gevaert N.V., Belgium, or its affiliates. The information and recommendations in this publication are believed to be accurate and are offered in good faith but do not constitute specifications. Suggestions concerning uses and applications are only the opinion of Agfa-Gevaert N.V. and users should carry out their own testing procedures to confirm suitability for their purposes. Agfa-Gevaert N.V. MAKES NO WARRANTY OF ANY KIND AND EXCLUDES ANY STATUTORY WARRANTY EXPRESS OR IMPLIED other than that materials conform to their current applicable standard specification. Statements herein therefore should not be construed as guarantees of satisfactory quality or fitness for purpose. The responsibility of Agfa-Gevaert N.V. for claims arising out of breach of guarantee, negligence, strict liability or otherwise is limited to the purchase price of the material. Suggestions concerning working practices and procedures are based on the practices adopted by existing users of the products and are made in good faith. IT IS THE RESPONSIBILITY OF THE USER TO ENSURE THAT ALL RELEVANT HEALTH AND SAFETY LAWS AND REGULATIONS ARE COMPLIED WITH. Agfa-Gevaert N.V. does not provide any advice on such laws and regulations and accepts no responsibility, express or implied, for breach of such regulations. Statements concerning the use of products described herein should not be construed as recommending the infringement of any patent and no liability for infringement arising out of such use is assumed.